

Top View


**INSTALLATION DETAILS (Recommendations only)**

*Concrete footings, 25mPa:*


- Two 500x500x500mm minimum footing size
  - Bolt down to footings with 4x M12x75mm Dynabolts or similar
  - For extended leg option, set product(s) into footings
- or

*Concrete slab, 25mPa:*


- One 1900x900x100mm (minimum) thick slab recommended





Perspective View



Right View




Front View



500

750

500



Ground level



Commercial Systems Australia Pty. Ltd.  
 42 Orchard St, Kilsyth South, VIC  
 phone: (03) 9723 4111  
 fax: (03) 9723 3494  
 email: design@commercialsystems.com.au

Model Code: TM4612  
 Model Description: Vivid Table

**Drawing: CS2365**

Sheet Number: 1  
 Sheet Description: Product overview


Drawn By: K.Sohanpal  
 Date Drawn: 15.09.2015  
 Revision Number: 0  
 Revision Details: -

SCALE 1:1


ALL DIMENSIONS IN MILLIMETERS  
 UNLESS OTHERWISE STATED  
 ALL PARTS CENTRED UNLESS SPECIFIED

TOLERANCES


X	+/- 1mm
X.X	+/- 0.5mm
X.XX	+/- 0.05mm



Top View



Front View



**INSTALLATION DETAILS (Recommendations only)**

**Concrete footings, 25mPa:**

- Table: Two 500x500x500mm minimum footing size
- Bench: Four 300x300x300mm minimum footing size
- Bolt down to footings with 12x M12x75mm Dynabolts or similar
- For extended leg option, set product(s) into footings

**or**  
**Concrete slab, 25mPa:**

- One 2000x2000x100mm (minimum) thick slab recommended



Commercial Systems Australia Pty. Ltd.  
 42 Orchard St, Kilsyth South, VIC  
 phone: (03) 9723 4111  
 fax: (03) 9723 3494  
 email: design@commercialsystems.com.au

Model Code: TM4612  
 Model Description: Vivid Table

**Drawing: CS2365**

Sheet Number: 1  
 Sheet Description: Product overview

Drawn By: K.Sohanpal  
 Date Drawn: 15.09.2015

Revision Number: 0  
 Revision Details: -

SCALE 1:1

ALL DIMENSIONS IN MILLIMETERS  
 UNLESS OTHERWISE STATED  
 ALL PARTS CENTRED UNLESS SPECIFIED

TOLERANCES

X +/- 1mm  
 X.X +/- 0.5mm  
 X.XX +/- 0.05mm